

HOW TO ORDER

STEP 1 » Choose Recessed Poke-Through (MOI6-REC)



MOI6-REC

STEP 2 » Choose Configuration *

*Configuration does not include communication components

	DP-C8 » USB receptacle & (8) communication openings
	DP-DPUSB(AC) » (1) Decora receptacle & (1) 2USB (AC) receptacle
	DP2 » (2) Decora receptacle
	DPUSB(AC)-C8 » (1) 2USB (AC) receptacle & (8) communication openings
	DPUSB(AC)2 » (2) 2USB (AC) receptacles
	P2-AV-C6 » (2) Power & (1) 6-port AV & (6) communication openings
	P2-AV2 » (2) Power & (2) 6-port AV
	P2-DP-C6 » (2) Power & (1) Decora receptacle & (6) communication openings

	P2-DPUSB(AC)-C6 » (2) Power & 2USB (AC) receptacle & (6) communication openings
	P4-AV-C2 » (4) Power & (1) 6-port AV & (2) communication openings
	P4-C4-AV1.5 » (4) Power & (4) communication openings & 1.5 inch AV opening
	P4-C8 » (4) Power & (8) communication openings
	P4-DP » (4) Power & (1) Decora receptacle
	P4-DPUSB(AC) » (4) Power & 2USB (AC) receptacle
	P6-C4 » (6) Power & (4) communication openings

EXAMPLE:
 MOI6-REC-P4-C8

STEP 3 » Choose Cover Finish (AHC-CED Cover only for MOI6-REC)


Stainless Steel
 Add: **-SS**


Brass
 Add: **-BR**


Black
 Add: **-BK**

EXAMPLE

MOI6-REC-P4-C8-SS-AHC-CED

